

**CABTITE BP 10MM PA****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The blanking plugs are used for the safe closing of un-needed cable passages in the sealing elements.

**General ordering data**

|            |  |
|------------|--|
| Version    | Blind plug, Cabtite (cable entry system), Polyamide, white, Height: 16 mm, Width: 10 mm, Depth: 16 mm, -40 °C...120 °C, IP66 |
| Order No.  | <a href="#">2652380000</a>   |
| Type       | CABTITE BP 10MM PA   |
| GTIN (EAN) | 4050118662481  |
| Qty.       | 25 pc(s).  |

**CABTITE BP 10MM PA****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|          |       |                 |            |
|----------|-------|-----------------|------------|
| Depth    | 16 mm | Depth (inches)  | 0.63 inch  |
| Height   | 16 mm | Height (inches) | 0.63 inch  |
| Width    | 10 mm | Width (inches)  | 0.394 inch |
| Length   | 16 mm | Length (inches) | 0.63 inch  |
| Diameter | 10 mm | Net weight      | 0.022 g    |

**Temperatures**

|                       |                  |
|-----------------------|------------------|
| Operating temperature | -40 °C... 120 °C |
|-----------------------|------------------|

**General information**

|                            |       |                            |           |
|----------------------------|-------|----------------------------|-----------|
| Halogen                    | No    | Material                   | Polyamide |
| Outer cable diameter, max. | 10 mm | Outer cable diameter, min. | 10 mm     |
| Protection degree          | IP66  | UL 94 flammability rating  | V-0       |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000879    | ETIM 7.0    | EC000879    |
| ETIM 8.0    | EC000879    | ETIM 9.0    | EC000879    |
| ECLASS 9.0  | 27-14-44-21 | ECLASS 9.1  | 27-14-44-21 |
| ECLASS 10.0 | 27-14-44-21 | ECLASS 11.0 | 27-14-44-21 |
| ECLASS 12.0 | 27-14-08-07 | ECLASS 13.0 | 27-14-08-07 |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                    |   |
|--------------------|---|
| Engineering Data   | <a href="#">CAD data – STEP</a>                   |
| User Documentation | <a href="#">Cabtite Installation Instructions</a> |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>          |