

FIT 25 GN**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Our feed-in modules facilitate handling when feeding the system. For example, the bending radius of the cable can be reduced by using a feed-in module with side entry.

General ordering data

Version	Auxiliary connection (terminal), 25 mm ²
Order No.	2659050000
Type	FIT 25 GN
GTIN (EAN)	4050118671483
Qty.	10 pc(s).

FIT 25 GN**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	19.5 mm	Depth (inches)	0.768 inch
Height	34 mm	Height (inches)	1.339 inch
Width	13.5 mm	Width (inches)	0.531 inch
Net weight	10 g		

Material data

Colour	grey
--------	------

Rating data

Rated cross-section	25 mm ²	Rated current	101 A
---------------------	--------------------	---------------	-------

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-92
ECLASS 12.0	27-14-11-92	ECLASS 13.0	27-25-03-08

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--