

CB-UVR 140/3,5 BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

UV-resistant polyamide 6.6 ensures long durability of our special cable ties even with strong UV radiation. Ideal for continuous outdoor use.

General ordering data

| | |
|------------|---|
| Version | Cable ties, 3.5 x 140 mm, Polyamide 66, 130 N |
| Order No. | 2659320000 |
| Type | CB-UVR 140/3,5 BK |
| GTIN (EAN) | 4050118682687 |
| Qty. | 100 pc(s). |

CB-UVR 140/3,5 BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|--------|-----------------|------------|
| Height | 140 mm | Height (inches) | 5.512 inch |
| Width | 3.5 mm | Width (inches) | 0.138 inch |
| Net weight | 0.6 g | | |

Temperatures

| | | | |
|----------------------------------|-------------|----------------------------------|--------|
| Operating temperature range | -40...85 °C | Continuous operating temp., min. | -40 °C |
| Continuous operating temp., max. | 105 °C | | |

Installation materials

| | | | |
|-----------------------------------|-------|-----------------------------------|--------------|
| Bundle diameter, max. | 32 mm | Bundle diameter, min. | 2.5 mm |
| Cable diameter, max. | 35 mm | For re-opening | No |
| Halogen | No | Material | Polyamide 66 |
| Operating temperature range, max. | 85 °C | Operating temperature range, min. | -40 °C |
| Tensile strength | 130 N | Tensile strength (Pound-force) | 29 lbf |
| UL 94 flammability rating | V-2 | UV-resistant | Yes |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000046 | ETIM 7.0 | EC000046 |
| ETIM 8.0 | EC000046 | ETIM 9.0 | EC000046 |
| ECLASS 9.0 | 27-14-07-02 | ECLASS 9.1 | 27-14-07-02 |
| ECLASS 10.0 | 27-14-07-02 | ECLASS 11.0 | 27-14-07-02 |
| ECLASS 12.0 | 27-14-07-02 | ECLASS 13.0 | 27-14-07-02 |

Approvals

Approvals



| | |
|-----------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (UR) | E317499 |

Downloads

| | |
|---|--|
| Approval/Certificate/Document of Conformity | EU Declaration of Conformity |
| Catalogues | Catalogues in PDF-format |

CB-UVR 140/3,5 BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

