

**CB-VT 98/2,5 WT****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

Our self-extinguishing cable ties are suitable for environments with increased fire protection requirements. They comply with EN45545 and are suitable for use in rail vehicles.

**General ordering data**

Version	Cable ties, 2.5 x 98 mm, Polyamide 66, 80 N
Order No.	<a href="#">2659490000</a>
Type	CB-VT 98/2,5 WT
GTIN (EAN)	4050118682953
Qty.	100 pc(s).

**CB-VT 98/2,5 WT****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Height	98 mm	Height (inches)	3.858 inch
Width	2.5 mm	Width (inches)	0.098 inch
Net weight	0.24 g		

**Temperatures**

Operating temperature range	-40...85 °C	Continuous operating temp., min.	-40 °C
Continuous operating temp., max.	85 °C		

**Installation materials**

Bundle diameter, max.	21 mm	Bundle diameter, min.	1 mm
Cable diameter, max.	21 mm	For re-opening	No
Halogen	No	Material	Polyamide 66
Operating temperature range, max.	85 °C	Operating temperature range, min.	-40 °C
Tensile strength	80 N	Tensile strength (Pound-force)	18 lbf
UL 94 flammability rating	V-0	UV-resistant	No

**Classifications**

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ETIM 9.0	EC000046
ECLASS 9.0	27-14-07-02	ECLASS 9.1	27-14-07-02
ECLASS 10.0	27-14-07-02	ECLASS 11.0	27-14-07-02
ECLASS 12.0	27-14-07-02	ECLASS 13.0	27-14-07-02

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">EU Declaration of Conformity</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

### CB-VT 98/2,5 WT

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

