

WPC WAGON 115V**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Optional accessories to customise the Wire Processing Center. Cable feeding system directly on the workshop trolley or on an external unit, additional printers or gripper trays.

General ordering data

Version	Automatic machines
Order No.	2728480000
Type	WPC WAGON 115V
GTIN (EAN)	4050118811346
Qty.	1 pc(s).

WPC WAGON 115V

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	750 mm	Depth (inches)	29.528 inch
Height	1,800 mm	Height (inches)	70.866 inch
Width	1,100 mm	Width (inches)	43.307 inch
Net weight	30,000 g		

PW65 maintenance - automatic stripping/crimping

Compressed-air connection	5.5 bar	Electrical connection	100 - 240 V AC / 50/60 Hz
---------------------------	---------	-----------------------	---------------------------

Automatic cutting

Compressed-air connection	5.5 bar	Electrical connection	100 - 240 V AC / 50/60 Hz
---------------------------	---------	-----------------------	---------------------------

WPC

Electrical connection	100 - 240 V AC / 50/60 Hz	Display	15-inch touchscreen
Note	Load capacity max. 180 kg, Mobile use, Panel with completed cabling and additional mains plugs and USB connections, pivoting display holder	Compressed-air connection	5.5 bar

Classifications

ETIM 6.0	EC002224	ETIM 7.0	EC011808
ETIM 8.0	EC011808	ETIM 9.0	EC011808
ECLASS 9.1	21-07-03-08	ECLASS 10.0	21-07-03-08
ECLASS 11.0	21-07-03-08	ECLASS 12.0	21-07-03-08
ECLASS 13.0	21-07-03-08		

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--