

IE-CSPD5UD0100LSSVAP-X**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	System cable, M12 L-code – IP 67 straight socket, PushPull Power, PUR, 10 m
Order No.	2732640100
Type	IE-CSPD5UD0100LSSVAP-X
GTIN (EAN)	4064675022015
Qty.	1 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2024-02-27

IE-CSPD5UD0100LSSVAP-X**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Length	10 m	Length (inches)	393.701 inch
Net weight	1,000 g		

Temperatures

Operating temperature	-25 °C...75 °C
-----------------------	----------------

Cable specific standards

Standard, sheathing material	20939 (80 °C / 600 V)
------------------------------	-----------------------

Electrical properties

Rated current	16 A	Rated voltage	24 V
---------------	------	---------------	------

General standards

Connector standard	in accordance with PROFINET specification, IEC 61076-2-111
--------------------	--

Standards

Connector standard	in accordance with PROFINET specification, IEC 61076-2-111	Standard, sheathing material	20939 (80 °C / 600 V)
--------------------	--	------------------------------	-----------------------

Cable structure

Colour coding	brown, white, blue, black, grey	Cross-section	5*1.5 mm ²
Insulation	PP	Material sheath	PUR
Number of wires	5	Sheath diameter, max.	8.2 mm
Sheath diameter, min.	7.8 mm	Sheathing colour	Silver grey
Shielding	unshielded		

Mechanical and material properties of cable

Acceleration	5 m/s ²	Halogen	No
Min. bending radius, once only	4 x cable diameter	Min. bending radius, repetitive	7.5 x cable diameter

Plug

Plug left	M12, L-coded, IP67, male contact, straight, plug, Plastic, unshielded	Plug right	PushPull Power, IP67, fe- male contact, straight, plug, Zinc diecast, un- shielded
-----------	---	------------	---

Plug, left

Plug left	M12, L-coded, IP67, male contact, straight, plug, Plastic, unshielded
-----------	---

IE-CSPD5UD0100LSSVAP-X**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Plug, right**

Plug right

PushPull Power, IP67, female contact, straight, plug, Zinc diecast, unshielded

Classifications

ETIM 6.0	EC000993	ETIM 7.0	EC003248
ETIM 8.0	EC003248	ETIM 9.0	EC003248
ECLASS 9.0	27-06-20-01	ECLASS 9.1	27-06-23-90
ECLASS 10.0	27-06-01-05	ECLASS 11.0	27-06-01-05
ECLASS 12.0	27-06-01-05	ECLASS 13.0	27-06-01-05

Approvals

ROHS

Conform

Downloads

Catalogues

[Catalogues in PDF-format](#)

IE-CSPD5UD0100LSSVAP-X**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Blank**

TM-I is an acknowledged and accredited marker type for traffic engineering applications. There are various different tag lengths available for individual labelling with long character strings. Easy handling of separation and installation thanks to the project marker field. Pre-attachment of sleeves and retrofitting of tags offer excellent versatility

The special contour of TM-I allows easy assembly and secures firm positioning. They are compatible with a number of commercially available sleeves. Thanks to the MultiCard format, the tags can be printed quickly and conveniently with the PrintJet CONNECT, plotter or the STI pen.

- Easy handling of separation and installation thanks to the project marker field.
- Acknowledged and accredited marker for traffic engineering applications
- Pre-attachment of sleeves and retrofitting of tags offer excellent versatility
- Not suited for labelling with P-Ink or STI pen in connection with CLI T sleeves

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	TM-I 18 MC NE WS	Version
Order No.	1718431044	TM-I, Insert markers, 18 x 4 mm, white
GTIN (EAN)	4008190349011	
Qty.	320 pc(s).	

IE-CSPD5UD0100LSSVAP-X**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Blank**

TM-I is an acknowledged and accredited marker type for traffic engineering applications. There are various different tag lengths available for individual labelling with long character strings. Easy handling of separation and installation thanks to the project marker field. Pre-attachment of sleeves and retrofitting of tags offer excellent versatility

The special contour of TM-I allows easy assembly and secures firm positioning. They are compatible with a number of commercially available sleeves. Thanks to the MultiCard format, the tags can be printed quickly and conveniently with the PrintJet CONNECT, plotter or the STI pen.

- Easy handling of separation and installation thanks to the project marker field.
- Acknowledged and accredited marker for traffic engineering applications
- Pre-attachment of sleeves and retrofitting of tags offer excellent versatility
- Not suited for labelling with P-Ink or STI pen in connection with CLI T sleeves

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	TM-I 12 MC NE WS	Version
Order No.	1718411044	TM-I, Insert markers, 12 x 4 mm, white
GTIN (EAN)	4008190348977	
Qty.	320 pc(s).	