

**CA 100 DUO****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

**General ordering data**

Version	Automatic stripper and crimper
Order No.	<a href="#">2740900000</a>
Type	CA 100 DUO
GTIN (EAN)	4050118835700
Qty.	1 pc(s).
Replacement parts	<a href="#">2007380000</a> <a href="#">2912430000</a>

## CA 100 DUO

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	550 mm	Depth (inches)	21.653 inch
Height	440 mm	Height (inches)	17.323 inch
Width	415 mm	Width (inches)	16.339 inch
Net weight	40,000 g		

## PW65 maintenance - automatic stripping/crimping

Compressed-air connection	5 - 5.5 bar	Consumables	with plastic collar
Crimping	Trapezoidal	Crimping length	8 - 18 mm
Drive	Electropneumatic	Electrical connection	100-240 V / 50/60 Hz / 100 VA
Pulse time	approx. 3 s	Stripping range	6 - 10 mm <sup>2</sup> (4 mm <sup>2</sup> opt.) / AWG 10-8 (AWG 12 opt.)

## Classifications

ETIM 6.0	EC002778	ETIM 7.0	EC002778
ETIM 8.0	EC002778	ETIM 9.0	EC002778
ECLASS 9.0	17-13-01-01	ECLASS 9.1	17-13-01-01
ECLASS 10.0	17-13-01-01	ECLASS 11.0	17-13-01-01
ECLASS 12.0	17-13-01-01	ECLASS 13.0	17-13-01-01

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

## Approvals

Approvals



ROHS	Conform
------	---------

## Downloads

User Documentation	<a href="#">Flyer - CA 100 DUO</a> <a href="#">Manual CA 100 DUO EN DE</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>