

BIT E6.3 1.0X5.5X110**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection

Slot-head bits DIN 5264, 1/4" drive, E6.3 DIN 3126

General ordering data

Version	Screwdriver insert, Blade width (B): 5.5 mm, Blade length: 110 mm, Blade thickness (A): 1 mm
Order No.	2749080000
Type	BIT E6.3 1.0X5.5X110
GTIN (EAN)	4050118895384
Qty.	5 pc(s).

BIT E6.3 1.0X5.5X110**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Width	110 mm	Width (inches)	4.331 inch
Net weight	21 g		

Technical data

Description of article	Bit with slotted blade, 0.5 x 3.0 x 110
------------------------	--

Screwing tools

Blade length	110 mm	Blade thickness (A)	1 mm
Blade width (B)	5.5 mm	Form	E 6.3 DIN 3126, Slotted

Classifications

ETIM 6.0	EC002116	ETIM 7.0	EC002116
ETIM 8.0	EC003864	ETIM 9.0	EC003864
ECLASS 9.1	21-04-04-90	ECLASS 10.0	21-04-04-90
ECLASS 11.0	21-04-42-04	ECLASS 12.0	21-04-42-04
ECLASS 13.0	21-04-42-04		

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--