

BIT E6.3Z 0.6X3.5X70**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection

Slot-head bits DIN 5264, 1/4" drive, E6.3 DIN 3126

General ordering data

Version	Screwdriver insert, Blade width (B): 3.5 mm, Blade length: 70 mm, Blade thickness (A): 0.6 mm
Order No.	2749100000
Type	BIT E6.3Z 0.6X3.5X70
GTIN (EAN)	4050118895407
Qty.	5 pc(s).

BIT E6.3Z 0.6X3.5X70**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Width	70 mm	Width (inches)	2.756 inch
Net weight	10 g		

Technical data

Description of article	Bit with pilot tip
------------------------	--------------------

Screwing tools

Blade length	70 mm	Blade thickness (A)	0.6 mm
Blade width (B)	3.5 mm	Form	E 6.3 DIN 3126, With assembly peg, Slotted

Classifications

ETIM 6.0	EC002116	ETIM 7.0	EC002116
ETIM 8.0	EC003864	ETIM 9.0	EC003864
ECLASS 9.1	21-04-04-90	ECLASS 10.0	21-04-04-90
ECLASS 11.0	21-04-42-04	ECLASS 12.0	21-04-42-04
ECLASS 13.0	21-04-42-04		

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--