

**SDS 0.4X2.0X60****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Slotted screwdriver with rounded blade SD DIN 5265,  
ISO 2380/2, output to DIN 5264, ISO 2380/1. Chrom-  
Top tip, SoftFinish grip

**General ordering data**

Version	Screwdriver, Blade width (B): 2 mm, Blade length: 60 mm, Blade thickness (A): 0.4 mm
Order No.	<a href="#">2749260000</a>
Type	SDS 0.4X2.0X60
GTIN (EAN)	4050118895537
Qty.	1 pc(s).

**SDS 0.4X2.0X60****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Length	165 mm	Length (inches)	6.496 inch
Net weight	4 g		

**Technical data**

Description of article	Screwdriver with slotted bit, 0.4 x 2	Version	straight
------------------------	---------------------------------------	---------	----------

**Screwing tools**

Blade length	60 mm	Blade thickness (A)	0.4 mm
Blade type	B	Blade width (B)	2 mm
Form	Slotted		

**Classifications**

ETIM 6.0	EC000158	ETIM 7.0	EC000158
ETIM 8.0	EC000158	ETIM 9.0	EC000158
ECLASS 9.0	21-04-04-07	ECLASS 9.1	21-04-04-07
ECLASS 10.0	21-04-04-07	ECLASS 11.0	21-04-04-07
ECLASS 12.0	21-04-04-07	ECLASS 13.0	21-04-04-07

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	b28ab223-64ec-44cf-adb0-4dd6ebcae141

**Downloads**

Product Change Notification	<a href="#">Produktänderungsmitteilung</a> <a href="#">Product Change Notification</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>