

SDS 0.5X3.0X80**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Slotted screwdriver with rounded blade SD DIN 5265,
ISO 2380/2, output to DIN 5264, ISO 2380/1. Chrom-
Top tip, SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 3 mm, Blade length: 80 mm, Blade thickness (A): 0.5 mm
Order No.	2749330000
Type	SDS 0.5X3.0X80
GTIN (EAN)	4050118895551
Qty.	1 pc(s).

SDS 0.5X3.0X80**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Length	185 mm	Length (inches)	7.283 inch
Net weight	40 g		

Technical data

Description of article	Screwdriver with slotted bit, 0.5 x 3	Version	straight
------------------------	---------------------------------------	---------	----------

Screwing tools

Blade length	80 mm	Blade thickness (A)	0.5 mm
Blade type	A	Blade width (B)	3 mm
Form	Slotted		

Classifications

ETIM 6.0	EC000158	ETIM 7.0	EC000158
ETIM 8.0	EC000158	ETIM 9.0	EC000158
ECLASS 9.0	21-04-04-07	ECLASS 9.1	21-04-04-07
ECLASS 10.0	21-04-04-07	ECLASS 11.0	21-04-04-07
ECLASS 12.0	21-04-04-07	ECLASS 13.0	21-04-04-07

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	b28ab223-64ec-44cf-adb0-4dd6ebcae141

Downloads

Product Change Notification	Produktänderungsmitteilung Product Change Notification
Catalogues	Catalogues in PDF-format