

SDIS SLIM 0.6X3.5X100**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

Version	Mounting tool, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade thickness (A): 0.6 mm
Order No.	2749610000
Type	SDIS SLIM 0.6X3.5X100
GTIN (EAN)	4050118896350
Qty.	1 pc(s).

SDIS SLIM 0.6X3.5X100**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Length	205 mm	Length (inches)	8.071 inch
Net weight	40 g		

Technical data

Description of article	VDE-insulated screw-driver with slotted blade 0.6x3.5x100, SlimLine	Version	straight
------------------------	--	---------	----------

Screwing tools

Blade length	100 mm	Blade thickness (A)	0.6 mm
Blade width (B)	3.5 mm	Form	Slotted

Classifications

ETIM 6.0	EC000158	ETIM 7.0	EC000158
ETIM 8.0	EC000158	ETIM 9.0	EC000158
ECLASS 9.0	21-04-04-07	ECLASS 9.1	21-04-04-07
ECLASS 10.0	21-04-04-07	ECLASS 11.0	21-04-04-07
ECLASS 12.0	21-04-04-07	ECLASS 13.0	21-04-04-07

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Not affected

Downloads

Product Change Notification	Produktänderungsmitteilung Product Change Notification
Catalogues	Catalogues in PDF-format