

SDIS 0.4X2.0X60**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1.
SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 2 mm, Blade length: 60 mm, Blade thickness (A): 0.4 mm
Order No.	2749780000
Type	SDIS 0.4X2.0X60
GTIN (EAN)	4050118896527
Qty.	1 pc(s).

SDIS 0.4X2.0X60**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Width	164 mm	Width (inches)	6.457 inch
Length	165 mm	Length (inches)	6.496 inch
Net weight	40 g		

Technical data

Description of article	VDE-insulated screwdriver with slotted blade 0.4 x 2.0 x 60	Version	straight
------------------------	---	---------	----------

Screwing tools

Blade length	60 mm	Blade thickness (A)	0.4 mm
Blade type	A	Blade width (B)	2 mm
Form	Slotted		

Classifications

ETIM 6.0	EC000158	ETIM 7.0	EC000158
ETIM 8.0	EC000158	ETIM 9.0	EC000158
ECLASS 9.0	21-04-04-07	ECLASS 9.1	21-04-04-07
ECLASS 10.0	21-04-04-07	ECLASS 11.0	21-04-04-07
ECLASS 12.0	21-04-04-07	ECLASS 13.0	21-04-04-07

Downloads

Catalogues	Catalogues in PDF-format
------------	--