

SDIS 1.2X6.5X150**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 6.5 mm, Blade length: 150 mm, Blade thickness (A): 1.2 mm
Order No.	2749860000
Type	SDIS 1.2X6.5X150
GTIN (EAN)	4050118897067
Qty.	1 pc(s).

SDIS 1.2X6.5X150**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Length	265 mm	Length (inches)	10.433 inch
Net weight	113 g		

Technical data

Description of article	VDE-insulated screw-driver with slotted blade 1.2x6.5x150	Version	straight
------------------------	--	---------	----------

Screwing tools

Blade length	150 mm	Blade thickness (A)	1.2 mm
Blade type	B	Blade width (B)	6.5 mm
Form	Slotted		

Classifications

ETIM 6.0	EC000158	ETIM 7.0	EC000158
ETIM 8.0	EC000158	ETIM 9.0	EC000158
ECLASS 9.0	21-04-04-07	ECLASS 9.1	21-04-04-07
ECLASS 10.0	21-04-04-07	ECLASS 11.0	21-04-04-07
ECLASS 12.0	21-04-04-07	ECLASS 13.0	21-04-04-07

Downloads

Catalogues	Catalogues in PDF-format
------------	--