

SDIPM PH1 X 80**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

Version	Screwdriver, Blade width (B): 1 mm, 80 mm, Blade thickness (A): 1
Order No.	2749960000
Type	SDIPM PH1 X 80
GTIN (EAN)	4050118897265
Qty.	1 pc(s).

SDIPM PH1 X 80**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Width	185 mm	Width (inches)	7.283 inch
Net weight	46 g		

Technical data

Description of article	SlimLine, VDE-insulated crosshead screwdriver, Phillips size 1	Version	straight
------------------------	--	---------	----------

Screwing tools

Blade length	80 mm	Blade size, crosshead	1
Blade width (B)	1 mm	Form	Crosshead, Philips, round
Size	1		

Classifications

ETIM 6.0	EC000144	ETIM 7.0	EC000144
ETIM 8.0	EC000144	ETIM 9.0	EC000144
ECLASS 9.0	21-04-04-06	ECLASS 9.1	21-04-04-06
ECLASS 10.0	21-04-04-06	ECLASS 11.0	21-04-04-06
ECLASS 12.0	21-04-04-06	ECLASS 13.0	21-04-04-06