

SDIZ 0.8X4.0X100**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1.
SoftFinish grip

General ordering data

Version	Screwdriver, Blade length: 100 mm, Blade thickness (A): 0.8 mm
Order No.	2749990000
Type	SDIZ 0.8X4.0X100
GTIN (EAN)	4050118897296
Qty.	1 pc(s).

SDIZ 0.8X4.0X100**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Width	210 mm	Width (inches)	8.268 inch
Net weight	45 g		

Technical data

Description of article	VDE-insulated screwdriver with pilot tip 0.8 x 4.0 x 100
------------------------	--

Screwing tools

Blade length	100 mm	Blade thickness (A)	0.8 mm
Form	Slotted		

Classifications

ETIM 6.0	EC000149	ETIM 7.0	EC000149
ETIM 8.0	EC000149	ETIM 9.0	EC000149
ECLASS 9.0	21-04-04-07	ECLASS 9.1	21-04-04-90
ECLASS 10.0	21-04-50-03	ECLASS 11.0	21-04-50-03
ECLASS 12.0	21-04-50-03	ECLASS 13.0	21-04-50-03

Downloads

Catalogues	Catalogues in PDF-format
------------	--