

HDC-C-HE-BM0.5KO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	Heavy-duty connectors, Crimp contact, Female, Conductor cross-section, max.: 0.5
Order No.	2784160000
Type	HDC-C-HE-BM0.5KO
GTIN (EAN)	4064675060895
Qty.	10 pc(s).

HDC-C-HE-BM0.5KO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	1.8 g
------------	-------

General data

Conductor cross-section, max.	0.5 mm ²	Contact material	Copper alloy
Cross-section for connected wire	0.5 mm ²	Material	Copper alloy
Series	HE	Stripping length, rated connection	7.5 mm
Surface finish	Constantan	Type	Female
Type of connection	Crimp connection		

Classifications

ETIM 6.0	EC000796	ETIM 7.0	EC000796
ETIM 8.0	EC000796	ETIM 9.0	EC000796
ECLASS 9.0	27-44-02-04	ECLASS 9.1	27-44-02-04
ECLASS 10.0	27-44-02-04	ECLASS 11.0	27-44-02-04
ECLASS 12.0	27-44-02-04	ECLASS 13.0	27-44-02-04

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	6eabd5ae-2d6b-409e-8bdf-87c27ee10e40

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format