

IE-ANT-WL-DB-MIMO-PD-RPSMAM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Antennas and antenna accessories (coax cables and mounts)**

- State-of-the-art antennas
- Industry proven
- Robust design (up to IP67 protection)
- For outdoor and indoor use
- Latest technology support
- Up to Wi-Fi 6 and Wi-Fi 6E (2.4 GHz, 5 GHz, 6 GHz)
- Up to 5G (NR) support (700 MHz - 3.8 GHz)
- Also support for other technologies (e.g. Bluetooth, GNSS, etc.)
- Appropriate coax cables at different lengths
- Suitable pole and wall mounts

General ordering data

Version	Semi-directional antenna, Wi-Fi antenna, Up to Wi-Fi 6 & 6E (IEEE802.11ax), +/- 45° linear, 4x RP-SMA male, IP67, Impedance: 50 Ω
Order No.	2788080000
Type	IE-ANT-WL-DB-MIMO-PD-RPSMAM
GTIN (EAN)	4064675066347
Qty.	1 pc(s).

IE-ANT-WL-DB-MIMO-PD-RPSMAM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	198 mm	Depth (inches)	7.795 inch
Height	34 mm	Height (inches)	1.339 inch
Width	198 mm	Width (inches)	7.795 inch
Net weight	450 g		

Temperatures

Storage temperature	-40 °C...70 °C	Operating temperature	-40 °C...70 °C
---------------------	----------------	-----------------------	----------------

Enclosure material

Colour	white
--------	-------

Included in delivery

Included in delivery	1 x antenna
----------------------	-------------

Mechanical and material properties of cable

Cable length	0.78 m
--------------	--------

Technical data

Amount of antenna elements (MIMO)	4	Antenna gain	6 dBi, 5 dBi
Composite power max.	20 W	Frequency range	2.3-2.8 GHz, 4.9-7.125 GHz
Impedance	50 Ω	Polarisation	+/- 45° linear
Standing wave ratio	<2.0 typical, 2.5 max.	Type of connection	4x RP-SMA male

Environmental conditions

Operating temperature, max.	70 °C	Operating temperature, min.	-40 °C
Storage temperature, max.	70 °C	Storage temperature, min.	-40 °C
Wind load	200 km/h		

Classifications

ETIM 6.0	EC001698	ETIM 7.0	EC001698
ETIM 8.0	EC001698	ETIM 9.0	EC001698
ECLASS 9.0	19-07-01-05	ECLASS 9.1	19-07-01-05
ECLASS 10.0	19-07-01-05	ECLASS 11.0	19-07-01-05
ECLASS 12.0	19-07-01-05	ECLASS 13.0	19-07-01-05

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	e4cad7fc-a55e-4d5c-8f05-417a6385e9b6

Approvals

ROHS	Conform
------	---------

IE-ANT-WL-DB-MIMO-PD-RPSMAM

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data	CAD data – STEP
Product Change Notification	Product Change Notification
Technical Documentation	Radiation Pattern
User Documentation	Hardware Installation Guide
Catalogues	Catalogues in PDF-format

IE-ANT-WL-DB-MIMO-PD-RPSMAM

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories**Antennas and antenna accessories (coax cables and mounts)****Antennas and antenna accessories (coax cables and mounts)**

- State-of-the-art antennas
- Industry proven
- Robust design (up to IP67 protection)
- For outdoor and indoor use
- Latest technology support
- Up to Wi-Fi 6 and Wi-Fi 6E (2.4 GHz, 5 GHz, 6 GHz)
- Up to 5G (NR) support (700 MHz - 3.8 GHz)
- Also support for other technologies (e.g. Bluetooth, GNSS, etc.)
- Appropriate coax cables at different lengths
- Suitable pole and wall mounts

General ordering data

Type	IE-ANT-MOUNT-PANEL	Version
Order No.	2789830000	Antenna mount for "IE-ANT-WL-DB-MIMO-PD-RPSMAM"
GTIN (EAN)	4064675068341	
Qty.	1 pc(s).	