

**IE-TO-RJ45-C-ZP-C5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Mounting rail outlet, RJ45 junction design according to  
IEC 60603-7-51

**General ordering data**

Version	Mounting rail outlet, RJ45, IP20, Cat. 5
Order No.	<a href="#">2819260000</a>
Type	IE-TO-RJ45-C-ZP-C5
GTIN (EAN)	4064675330110
Qty.	10 pc(s).

**IE-TO-RJ45-C-ZP-C5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Net weight	15 g
------------	------

**Temperatures**

Operating temperature	-40 °C...80 °C
-----------------------	----------------

**General data**

Connection 1	RJ45	Connection 2	RJ45
Wiring	Coupling	Colour	beige, black
Housing main material	Plastic, PA 66 UL V0 E63957	Category	Cat. 5
Contact surface	Gold over nickel	Type of mounting	TS 35
Shielding	unshielded	Protection degree	IP20
Plugging cycles	750 (RJ45)		

**Electrical properties**

Current-carrying capacity at 50 °C	1 A	Dielectric strength, contact / contact	≥ 1000 V AC/DC
Dielectric strength, contact / shield	≥ 1500 V AC/DC	Rated voltage	50 V

**General standards**

Connector standard	IEC 60603-7-5 1
--------------------	-----------------

**Classifications**

ETIM 6.0	EC000313	ETIM 7.0	EC000313
ETIM 8.0	EC000313	ETIM 9.0	EC000313
ECLASS 9.0	27-44-03-20	ECLASS 9.1	19-17-01-25
ECLASS 10.0	27-44-03-20	ECLASS 11.0	27-44-03-20
ECLASS 12.0	27-44-03-20	ECLASS 13.0	27-44-03-20

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

## IE-TO-RJ45-C-ZP-C5

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

