

**BIT E6,3 T20 X 150****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The Weidmüller bits are standard bits which are highly popular with users thanks to their good quality, large range and efficiency. The computer-controlled hardening method enables Weidmüller to guarantee a consistently high standard of quality.

The high-quality raw materials used make it possible to reach torques far higher than any of those specified in the relevant DIN standards:

- DIN 5261 for PH/PZ bits,
- DIN 5263 for slotted bits,
- Camcar standard for TORX bits

That means a long life at high torques and hence ideal conditions for standard situations.

**The benefits:**

- Suitable for all types of screws. Because of their excellent hardness values of 59-61 HRC, they are suitable for use with both manual and power tools.
- Good wearing resistance and thus a long life expectancy.
- Optimum fit in all DIN screws means low wear and optimum torque transmission.
- Manufactured to meet professional quality criteria according to relevant ISO standards with a consistently high standard of quality.

**General ordering data**

Version	Mounting tool
Order No.	<a href="#">2821510000</a>
Type	BIT E6,3 T20 X 150
GTIN (EAN)	4064675359050
Qty.	50 pc(s).

**BIT E6,3 T20 X 150****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Width	150 mm	Width (inches)	5.905 inch
Net weight	2 g		

**Screwing tools**

Form	Torx®
------	-------

**Classifications**

ETIM 6.0	EC002117	ETIM 7.0	EC002117
ETIM 8.0	EC003864	ETIM 9.0	EC003864
ECLASS 9.0	21-04-42-02	ECLASS 9.1	21-01-90-90
ECLASS 10.0	21-04-42-02	ECLASS 11.0	21-04-42-02
ECLASS 12.0	21-04-42-02	ECLASS 13.0	21-04-42-02

**Approvals**

ROHS	Conform
------	---------