

ZQV 4N/2 WT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

General ordering data

Version	Cross-connector (terminal), Plugged, Number of poles: 20, Pitch in mm (P): 6.10, Insulated: Yes, 32 A, white
Order No.	2831800000
Type	ZQV 4N/2 WT
GTIN (EAN)	4064675417033
Qty.	60 pc(s).

ZQV 4N/2 WT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	28 mm	Depth (inches)	1.102 inch
Height	2.8 mm	Height (inches)	0.11 inch
Width	119.7 mm	Width (inches)	4.713 inch
Net weight	1.371 g		

Temperatures

Storage temperature	-25 °C...55 °C	Operating temperature	-60 °C...130 °C
---------------------	----------------	-----------------------	-----------------

Material data

Material	Wemid	Colour	white
UL 94 flammability rating	V-0		

Additional technical data

Type of fixing	Plugged
----------------	---------

Cross-connector

Rated current, multi-pole	32 A	Type	Cross-connector
---------------------------	------	------	-----------------

Dimensions

Pitch in mm (P)	6.1 mm
-----------------	--------

General

Number of poles	20
-----------------	----

Rating data

Rated current	32 A
---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

Important note

Product information	Due to stability and temperature reasons It is only possible to break out 60% of contact elements The usage of cross connectors reduces the rated voltage to 400VThe voltage reduced to 25V if cut cross connection with blank cut edges are used
---------------------	---

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format