

IE-C6GO6LR0008F40F40-X-K6KV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Wiring diagram**

LMN cable, RJ12 / RJ12, twisted-pair, suitable for smart metering applications, unshielded

General ordering data

Version	Patch cable, RJ12, RJ12, Cat.3, LSZH, 0.8 m, 6 kV
Order No.	2860910008
Type	IE-C6GO6LR0008F40F40-X-K6KV
GTIN (EAN)	4064675578659
Qty.	1 pc(s).

IE-C6GO6LR0008F40F40-X-K6KV

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	0.8 m	Length (inches)	31.496 inch
Net weight	6 g		

Temperatures

Operating temperature	-20 °C...60 °C
-----------------------	----------------

General standards

Application-specific communication cable facilities	VDE-AR-N 4100:2019-04	Connector standard	TIA-1096-A
---	-----------------------	--------------------	------------

Cable structure

Cable layout	Double insulation according to VDE 0603-100	Cross-section	3x2xAWG 24/7
Insulation	PE	Insulation cross-section	1 mm
Material sheath	LSZH	Number of wires	6
Sheath diameter	4.8 mm	Sheath diameter, max.	4.95 mm
Sheath diameter, min.	4.65 mm	Sheathing colour	red
Shielding	U/UTP		

Electrical properties of cable

Category	Cat.3	Insulation strength	≥ 100 MΩ
Insulation voltage, max.	500 V	Operating voltage	50 V
Rated current	1 A	Rated impulse withstand voltage	6 kV
Signal propagation time	5.45 ns/m		

Mechanical and material properties of cable

Colour	red	Halogen	No
Resistance to spread of flame	in accordance with IEC 60332-1		

Plug

Plug left	RJ12, IP20, male contact, straight, plug, unshielded	Plug right	RJ12, IP20, male contact, straight, plug, unshielded
-----------	--	------------	--

Classifications

ETIM 6.0	EC002599	ETIM 7.0	EC002599
ETIM 8.0	EC002599	ETIM 9.0	EC002599
ECLASS 9.0	27-06-03-08	ECLASS 9.1	27-06-03-08
ECLASS 10.0	27-06-03-08	ECLASS 11.0	27-06-03-08
ECLASS 12.0	27-06-03-08	ECLASS 13.0	27-06-03-08

Approvals

Approvals



ROHS Conform

Creation date May 9, 2024 9:34:47 AM CEST

Catalogue status 04.05.2024 / We reserve the right to make technical changes.

IE-C6GO6LR0008F40F40-X-K6KV

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Catalogues

[Catalogues in PDF-format](#)

IE-C6GO6LR0008F40F40-X-K6KV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Drawings****Drawing**