

CA-T2WB-10M-7.4/1P-R-BBG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The Mode 3 charging cables with ergonomic handle design offer charging comfort of the highest quality. Robust and durable in every respect: the housing is dirt and water repellent, shock and impact resistant as well as cold and heat resistant. Available in different lengths, in straight and spiral form, for 1- or 3-phase charging.

General ordering data

Version	AC charging cable, Connection type - charging point: free conductor end, Connection type - vehicle: Type 2, Charging power, max.: 7.4 kW, Number of phases: , Rated current: 32 A, Cable length:
Order No.	2861580000
Type	CA-T2WB-10M-7.4/1P-R-BBG
GTIN (EAN)	4064675581475
Qty.	1 pc(s).

CA-T2WB-10M-7.4/1P-R-BBG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Diameter	13.7 mm	Net weight	3,560 g
----------	---------	------------	---------

Cable

Cable colour	black	Cable type	regular
--------------	-------	------------	---------

Plug type

Connection type - charging point	free conductor end	Connection type - vehicle	Type 2
Plug colour	black, dark grey		

System requirements

Type of communication to vehicle	Control Pilot (CP), Proximity Pilot / Plug Present (PP)
----------------------------------	---

Approvals and norms

Approvals	IEC 62196-1, IEC 62196-2, EN 50620
-----------	------------------------------------

Classifications

ETIM 6.0	EC002897	ETIM 7.0	EC002897
ETIM 8.0	EC002897	ETIM 9.0	EC002897
ECLASS 9.0	27-14-47-05	ECLASS 9.1	27-14-47-05
ECLASS 10.0	27-14-47-05	ECLASS 11.0	27-14-47-05
ECLASS 12.0	27-14-47-05	ECLASS 13.0	27-14-47-05

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	f233b551-8efc-4a5f-b233-33b40f22269a

Downloads

Catalogues	Catalogues in PDF-format
------------	--