

PWEB-ES-RT-5000/10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

PROCON-WEB Embedded System is available platform independent via container image, Linux or Windows. To implement the optimal web-based HMI solution, PROCON-WEB Embedded System offers the following features:

- Roles and rights based user management
- Extensive alarming
- predefined controls, such as buttons, sliders, text fields or image areas
- powerful more complex controls, like iframes, charts, tables
- flexible scripting for maximum flexibility
- Historian functionality for storing and visualizing historical data
- connection to various control systems via extensive communication driver portfolio (OPC-UA, CODESYS driver or via Modbus)

General ordering data

| | |
|-----------|--|
| Version | Visualization software, Platform for runtime system: Linux, Windows 10, Windows 11, Docker, Number of process variables, max.: 5000, Number of HMI-devices, max.: 10 |
| Order No. | 2875340000 |
| Type | PWEB-ES-RT-5000/10 |
| Qty. | 1 pc(s). |

PWEB-ES-RT-5000/10

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | |
|------------|---|
| Net weight | 0 |
|------------|---|

Features of the runtime

| | | | |
|-----------------------------|---|-----------------------------|---------------------|
| Platform for runtime system | Linux, Windows 10, Windows 11, Docker | Number of HMI-devices, max. | 10 |
| Maximum number of drivers | 99 | Projectable by | PROCON-WEB Designer |
| Runtime features | Simple and complex controls, Alarming, Historian, User-Management, Process connection via communication drivers | | |

Licence information

| | | | |
|------------------|------------------|-----------------------------------|------------------|
| Licence coverage | One-time licence | Licence type | Software licence |
| Licensing by | WIBU Ticket ID | Number of process variables, max. | 5,000 |

System data

| | | | |
|-----------------------------|----------------------|-----------------------------------|---------------------------------------|
| Number of HMI-devices, max. | 10 | Number of process variables, max. | 5,000 |
| Operating system | Linux, Windows, u-OS | Platform for runtime system | Linux, Windows 10, Windows 11, Docker |

System requirements

| | | | |
|---------------------------|----------------------|-----------------------------|--------|
| Minimal disk space needed | 0.1 GB | Minimal memory (RAM) needed | 0.1 GB |
| Operating system | Linux, Windows, u-OS | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001416 | ETIM 7.0 | EC001416 |
| ETIM 8.0 | EC001416 | ETIM 9.0 | EC001416 |
| ECLASS 9.0 | 27-24-25-02 | ECLASS 9.1 | 27-24-25-02 |
| ECLASS 10.0 | 27-24-25-02 | ECLASS 11.0 | 27-24-25-02 |
| ECLASS 12.0 | 27-24-25-02 | ECLASS 13.0 | 27-24-25-02 |

Downloads

| | |
|-----------------------------|--|
| Product Change Notification | Release notes - PROCON-WEB ES 6.7.0 EN Release notes - u-OS App PROCON-WEB ES |
| Software | Software – PROCON-WEB Embedded System 6.7.0 for Windows |
| Catalogues | Catalogues in PDF-format |