

ZQV 4N/20**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

General ordering data

Version	Cross-connector (terminal), Plugged, Number of poles: 20, Pitch in mm (P): 6.00, Insulated: Yes, 32 A, orange
Order No.	2883800000
Type	ZQV 4N/20
GTIN (EAN)	4064675848769
Qty.	20 pc(s).

ZQV 4N/20**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	120.7 mm	Depth (inches)	4.752 inch
Height	2.8 mm	Height (inches)	0.11 inch
Width	27.95 mm	Width (inches)	1.1 inch
Net weight	0.78 g		

Temperatures

Storage temperature	-25 °C...55 °C	Operating temperature	-60 °C...130 °C
---------------------	----------------	-----------------------	-----------------

Material data

Material	Wemid	Colour	orange
UL 94 flammability rating	V-0		

Additional technical data

Explosion-tested version	No	Type of fixing	Plugged
Type of mounting	Plugged		

Cross-connector

Rated current, multi-pole	32 A	Type	Plug
---------------------------	------	------	------

Dimensions

Pitch in mm (P)	6 mm
-----------------	------

General

Number of poles	20
-----------------	----

Rating data

Rated current	32 A
---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

Important note

Product information	Due to stability and temperature reasons It is only possible to break out 60% of contact elements The usage of cross connectors reduces the rated voltage to 400V The voltage reduced to 25V if cut cross connection with blank cut edges are used
---------------------	--

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format