

SMARKLASER CENTER**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	Marking systems, Laser marking, MetalliCard on Roll
Order No.	2885190000
Type	SMARKLASER CENTER
GTIN (EAN)	4064675852834
Qty.	1 pc(s).

SMARKLASER CENTER

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	625 mm	Depth (inches)	24.606 inch
Height	1,800 mm	Height (inches)	70.866 inch
Width	1,425 mm	Width (inches)	56.102 inch
Floor space required	2225 x 1825 mm	Net weight	116,000 g

Temperatures

Humidity	10...85% (no condensation)
----------	----------------------------

Labelling systems

Included in delivery	Laser smoke exhaust, DVD with M-Print® PRO, Manual, SmarkLaser CENTER, Mobile underframe, External winder, Touchscreen 15 inch, Roll core	Interface	Ethernet
Marker type	MetalliCard on Roll	Operating system	Windows 7, Windows 8, Windows 8.1, Windows 10, Windows 11
Printing method	Laser marking	Software	M-Print® PRO
Voltage supply	230 V AC / 16 A		

SmarkLaser CENTER

Laserclass according to EN60825-1	Class 1
Noise level	below 67 dB (A) at a distance of one meter
Wavelength	Wavelength Laser typ. 1,064

Classifications

ETIM 6.0	EC000610	ETIM 7.0	EC000610
ETIM 8.0	EC000610	ETIM 9.0	EC000610
ECLASS 9.0	24-32-11-90	ECLASS 9.1	24-32-11-02
ECLASS 10.0	24-32-11-90	ECLASS 11.0	24-32-11-90
ECLASS 12.0	24-32-11-90	ECLASS 13.0	24-32-11-90

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--