

**IE-FCI-PWB-2USB-A/C-5V****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, FrontCom® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the FrontCom® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

**General ordering data**

Version	FrontCom, Insert Power large, USB charger
Order No.	<a href="#">2902340000</a>
Type	IE-FCI-PWB-2USB-A/C-5V
GTIN (EAN)	4099986004719
Qty.	1 pc(s).

## IE-FCI-PWB-2USB-A/C-5V

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	0 g
------------	-----

## Temperatures

Operating temperature	0 °C...45 °C
-----------------------	--------------

## General data

Insert type	Insert Power large	Protection degree	IP40
-------------	--------------------	-------------------	------

## USB charger

Charging sockets	1x USB A, 1x USB C	Input current	≤ 300 mA
Input voltage	100...240 V	Input voltage, max.	240 V
Input voltage, min.	100 V	Output current	3 A
Output voltage	5 V	Output voltage	5 V DC
Output voltage type	DC	Frequency range	50...60 Hz
Degree of efficiency	80%	Power consumption in standby mode	max. 0.1 W
Protection class	II	Standards	EN 60950-1, EN 62684

## Clampable conductors

Conductor connection cross-section, extremely flexible with wire end ferrule	1.5 ... 2.5 mm <sup>2</sup>
Conductor connection cross-section, extremely flexible with wire end ferrule	min. 1.5 mm <sup>2</sup>
	max. 2.5 mm <sup>2</sup>
Conductor connection cross-section, flexible with wire end ferrule	1.5 ... 2.5 mm <sup>2</sup>
Conductor connection cross-section, flexible with wire end ferrule	max. 2.5 mm <sup>2</sup>
	min. 1.5 mm <sup>2</sup>
Conductor connection cross-section, rigid	1.5 ... 2.5 mm <sup>2</sup>
Conductor connection cross-section, rigid	min. 1.5 mm <sup>2</sup>
	max. 2.5 mm <sup>2</sup>
Stripping length	6 mm
Type of connection	Screw connection

## Electrical properties

Degree of efficiency	80%
----------------------	-----

## Classifications

ETIM 6.0	EC001121	ETIM 7.0	EC001121
ETIM 8.0	EC001121	ETIM 9.0	EC001121
ECLASS 9.0	27-44-03-90	ECLASS 9.1	27-18-90-90
ECLASS 10.0	27-44-03-90	ECLASS 11.0	27-44-03-90
ECLASS 12.0	27-18-28-92	ECLASS 13.0	27-18-28-92

## Downloads

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--


## IE-FCI-PWB-2USB-A/C-5V

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

**Dimensioned drawing**



**Dimensioned drawing**

