

V-ZPA TERMINAL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	
Order No.	2904470000
Type	V-ZPA TERMINAL
GTIN (EAN)	4099986010352
Qty.	1 pc(s).

V-ZPA TERMINAL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	54.3 mm	Depth (inches)	2.138 inch
Height	220.4 mm	Height (inches)	8.677 inch
Width	12.5 mm	Width (inches)	0.492 inch
Net weight	160 g		

Temperatures

Operating temperature	-25 °C...55 °C
-----------------------	----------------

General data

Colour	grey	Rail	Busbar
--------	------	------	--------

Insulation coordination acc. to EN 50178

Pollution severity	3
--------------------	---

Rated data IEC / EN

Rated voltage (AC)	240 V	Voltage type	AC
--------------------	-------	--------------	----

Connection data

Wire connection method	Tension-clamp connection	Wire connection cross section, finely stranded, min.	1.5 mm ²
Wire connection cross section, finely stranded, max.	25 mm ²		

Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ETIM 9.0	EC000941
ECLASS 9.0	27-13-08-05	ECLASS 9.1	27-13-08-05
ECLASS 10.0	27-13-08-05	ECLASS 11.0	27-13-08-05
ECLASS 12.0	27-17-90-90	ECLASS 13.0	27-17-90-90

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	EU Konformitätserklärung / EU Declaration of Conformity
Engineering Data	CAD data – STEP
User Documentation	Beipackzettel / Instruction sheet
Catalogues	Catalogues in PDF-format