

UV66-ADV-15-CAP-W-V2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

u-view Advanced touch panels from Weidmüller offer excellent image quality and can be used in most industrial environments.

The portfolio features various screen sizes from 7" to 21.5" and has high-resolution capacitive touchscreens with support for swipe gestures and glove operation.

All panels are equipped with a Linux operating system and an HTML5-capable browser and are optimised for web applications through the integrated kiosk mode and their simple configuration.

As a result, they are the perfect solution for web-based visualisations and enable access to a variety of web servers, such as u-OS, u-create PROCON-WEB, u-control web and many more.

The panels have a particularly flat design, with an industrial IP66 housing.

General ordering data

Version	
Order No.	2932860000
Type	UV66-ADV-15-CAP-W-V2
GTIN (EAN)	4099986674189
Qty.	1 pc(s).

UV66-ADV-15-CAP-W-V2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	52 mm	Depth (inches)	2.047 inch
Height	269 mm	Height (inches)	10.591 inch
Width	419.7 mm	Width (inches)	16.524 inch
Net weight	3,780 g		

Temperatures

Humidity	95% relative humidity, non-condensing @ 40°C
----------	---

Equipment

Luminance	450 cd/m ²	Material display	Glass
Material frame	Aluminium coated	Number of displayable colours	16,200,000
Resolution	1920 x 1080	Size	15.6"
Touch-Screen	Projected capacitive (P-CAP)		

General data

Operating system	Linux Yocto 4.0.		
Protection degree	Built-in: IP66, Enclosure: IP20		
Voltage supply	24 V DC		
Voltage supply range	Voltage type	DC	
	Voltage, min.	19.2 V	
	Voltage, max.	28.8 V	

System data

Interfaces behind	1x Ethernet 10/100/1000 MBit/s (RJ45), 2x USB 2.0	Memory (Flash)	16 GB
Memory (RAM)	4 GB	Operating system	Linux Yocto 4.0.
Processor	NXP® ARM® Cor- tex™-A53 i.MX 8M Mini		

Classifications

ETIM 6.0	EC001412	ETIM 7.0	EC001412
ETIM 8.0	EC001412	ETIM 9.0	EC001412
ECLASS 9.0	27-33-02-01	ECLASS 9.1	27-33-02-01
ECLASS 10.0	27-33-02-01	ECLASS 11.0	27-33-02-01
ECLASS 12.0	27-33-02-01	ECLASS 13.0	27-33-02-01

Important note

Product information	Available from April 2024
---------------------	---------------------------

Approvals

ROHS	Conform
------	---------

UV66-ADV-15-CAP-W-V2

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data

[WM UV66-ADV-V2_datasheet](#)

[CAD data – STEP - UV66-ADV-15-CAP-W-V2](#)

[CAD data – STEP](#)

Catalogues

[Catalogues in PDF-format](#)


UV66-ADV-15-CAP-W-V2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com


Drawings

Maße (mm) / Dimensions (mm)



	LCD	A	B	C	D	E
UV66-ADV-7-CAP-W-V2	7"	205	146,9	25	52	7
UV66-ADV-10-CAP-W-V2	10.1"	283,1	202,3	25	52	7
UV66-ADV-15-CAP-W-V2	15.6"	419,7	269	25	52	7
UV66-ADV-21-CAP-W-V2	21.5"	558,4	349,8	25	52	7

Montageausschnitt / Panel cut-out



	LCD	F (mm)	G (mm)	R (mm)
UV66-ADV-7-CAP-W-V2	7"	192,4	139	5
UV66-ADV-10-CAP-W-V2	10.1"	274,1	193,3	5
UV66-ADV-15-CAP-W-V2	15.6"	411,9	261,2	5
UV66-ADV-21-CAP-W-V2	21.5"	549,8	341,3	5

u-view ECO, BASIC and ADVANCED

