

WIL-AXXXX-FXSF-5700-X800-GST**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Order No.	2979350000
Type	WIL-AXXXX-FXSF-5700-X800-GST
GTIN (EAN)	4099986832794
Qty.	1 pc(s).

WIL-AXXXX-FXSF-5700-X800-GST**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	135 mm	Depth (inches)	5.315 inch
Height	38 mm	Height (inches)	1.496 inch
Width	816 mm	Width (inches)	32.126 inch
Net weight	300 g		

Temperatures

Operating temperature	-20 - 45°C
-----------------------	------------

Connection data

Number of poles	3
-----------------	---

Electric data

Power	32.5 W	Dimmable	yes, stepless dimming
-------	--------	----------	-----------------------

General technical data

Light colour (CCT)	5700K, White	Light current	5,825 lm
Emitting angle	100 °	Operating life	60.000 h
Type of mounting	Screw mounting	Protection degree	IP40

Material data

Housing main material	hard anodised aluminium
-----------------------	-------------------------

Classifications

ETIM 6.0	EC000996	ETIM 7.0	EC000996
ETIM 8.0	EC000996	ETIM 9.0	EC000996
ECLASS 9.1	27-11-06-35	ECLASS 10.0	27-11-06-35
ECLASS 11.0	27-11-06-35	ECLASS 12.0	27-11-06-35
ECLASS 13.0	27-11-06-35		

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	------------------------------------------