

HDC HA 3 MP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Order No.	2985540000
Type	HDC HA 3 MP
GTIN (EAN)	4099986848559
Qty.	1 pc(s).

HDC HA 3 MP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	21 mm	Depth (inches)	0.827 inch
Height	28.5 mm	Height (inches)	1.122 inch
Width	28 mm	Width (inches)	1.102 inch
Net weight	12.78 g		

Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

Dimensions

Width	28 mm
-------	-------

General data

Colour	Light Grey	Free from halogens	false
Insulating material	PC	Material	Polycarbonate
Number of poles	3	Plugging cycles	≥ 500
Pollution severity	3	Rated current (DIN EN 61984)	10 A
Rated impulse voltage (DIN EN 61984)	4 kV	Rated voltage (DIN EN 61984)	48 V
Series	ModuPlug	Type	Male
Type of connection	PUSH IN	UL 94 flammability rating	V-0
Protection degree	IP20		

Connection data PE

Connection type PE	PUSH IN connection
--------------------	--------------------

Version

Conductor cross-section, max.	0.14 mm ²	Conductor cross-section, min.	1.5 mm ²
Material	Polycarbonate	Stripping length, rated connection	10 mm
Type of connection	PUSH IN		

Classifications

ETIM 6.0	EC002312	ETIM 7.0	EC002312
ETIM 8.0	EC002312	ETIM 9.0	EC002312
ECLASS 9.0	27-44-02-92	ECLASS 9.1	27-44-02-18
ECLASS 10.0	27-44-02-92	ECLASS 11.0	27-44-02-92
ECLASS 12.0	27-44-02-92	ECLASS 13.0	27-44-02-92

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--