

WBC-P-10BK-70**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Battery storage systems are playing an increasingly important role in the field of renewable energies. They usually consist of several individual batteries that need to be quick and easy to replace. The Weidmüller Battery Connector (WBC) makes it possible to connect several individual batteries to an ESS in just a few simple steps – and to disconnect the connections just as quickly if required. For more safety and easy handling, the poles are clearly marked: The positive pole in orange and the negative pole in black.

General ordering data

| | |
|------------|----------------------------|
| Order No. | 2991900000 |
| Type | WBC-P-10BK-70 |
| GTIN (EAN) | 4099986868717 |
| Qty. | 5 pc(s). |

WBC-P-10BK-70

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | |
|------------|--------|
| Net weight | 72.5 g |
|------------|--------|

Temperatures

| | | | |
|----------------------------------|--------|----------------------------------|--------|
| Continuous operating temp., min. | -40 °C | Continuous operating temp., max. | 125 °C |
|----------------------------------|--------|----------------------------------|--------|

General Data

| | | | |
|-------------------------------|--------------------|--------------------------|------------------|
| Approvals | UL 4128 | Colour | black |
| Conductor cross-section, max. | 70 mm ² | Contact diameter, male Ø | 10 mm |
| Material | PA 66 | Surface finish | silver |
| Type | Female | Type of connection | Crimp connection |

Technical Data

| | | | |
|---------------------------|-------|-------------------|--------------------|
| Plugging cycles | ≥ 100 | Protection degree | IP20, IP67 plugged |
| Rated current | 250 A | Rated voltage | 1,500 V |
| UL 94 flammability rating | V-0 | Volume resistance | ≥ 5000 MΩ |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 7.0 | EC001121 | ETIM 8.0 | EC001121 |
| ETIM 9.0 | EC001121 | ECLASS 10.0 | 27-44-03-12 |
| ECLASS 11.0 | 27-44-03-12 | ECLASS 12.0 | 27-44-03-12 |
| ECLASS 13.0 | 27-44-03-12 | | |

Approvals

Approvals



| | |
|-----------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (UR) | E529699 |

Downloads


| | |
|--------------------|--|
| User Documentation | Suitable Tools for WBC Battery Connector |
| Catalogues | Catalogues in PDF-format |

WBC-P-10BK-70

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



WBC-P-10BK-70

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Tools

**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 400 mm²
- 360° revolving quick action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- Additional features for APG series:
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB

General ordering data

| | | |
|------------|----------------------------|---------------------------------------|
| Type | APG 80 | Version |
| Order No. | 2853270000 | 6mm ² , 400mm ² |
| GTIN (EAN) | 4064675477020 | |
| Qty. | 1 pc(s). | |

... for crimp cable lugs (acc. to DIN 46234)**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 400 mm²
- 360° revolving quick action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- Additional features for APG series:
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB

General ordering data

| | | |
|------------|----------------------------|----------------------------------|
| Type | ES APG 80 DIN 70 | Version |
| Order No. | 1502890000 | 70mm ² , Indent crimp |
| GTIN (EAN) | 4050118310719 | |
| Qty. | 1 pc(s). | |