

FUSE WSFL 10X85 20A 1K5V GPV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



gPV 10×85 cylindrical fuse cartridges are designed to provide compact, safe and economical protection of photovoltaic modules (field protection) with voltages up to 1,500 DC. They provide protection against both overload and short circuit (gPV class according to the requirements of IEC60269-6 and UL248-19 standards).

Általános rendelési adatok

Verzió	Fotovoltaikus egységek, Olvadásbiztosíték-betét, 1500 V, 10x85, gPV, 20 A
Rendelési szám	4000002587
Típus	FUSE WSFL 10X85 20A 1K5V GPV
GTIN (EAN)	8430243419635
Qty.	50 Stück

FUSE WSFL 10X85 20A 1K5V GPV

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Műszaki adatok

Méretetek és tömegek

Magasság	85 mm	Magasság (coll)	3,346 inch
Szélesség	10,3 mm	Szélesség (coll)	0,406 inch
Nettó tömeg	1,94 g		

Biztosítóbetétek

Biztosítóbetétek, szabványok	IEC 60269-6	Áram	20 A
Névleges DC feszültség	1 500 V		

Besorolások

ETIM 7.0	EC002704	ETIM 8.0	EC002704
ETIM 9.0	EC002704	ECLASS 11.0	27-14-20-02
ECLASS 12.0	27-14-20-02	ECLASS 13.0	27-14-20-02

Tanúsítványok

ROHS	Megfelel
------	----------

Letöltések

Engineering Data	CAD data – Advanced Datasheet
Katalógusok	Catalogues in PDF-format