

FUSE WSFL 10X85 20A 1K5V GPV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

gPV 10×85 cylindrical fuse cartridges are designed to provide compact, safe and economical protection of photovoltaic modules (field protection) with voltages up to 1,500 DC. They provide protection against both overload and short circuit (gPV class according to the requirements of IEC60269-6 and UL248-19 standards).

Allmänna beställningsdata

Artikelbeteckning	Fotovoltaik, Smältsäkringsinsats, 1500 V, 10x85, gPV, 20 A
Art.nr.	4000002610
Typ	FUSE WSFL 10X85 20A 1K5V GPV
GTIN (EAN)	8430243419635
Förp.	50 Stück

FUSE WSFL 10X85 20A 1K5V GPV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Tekniska data****Mått och vikter**

Höjd	85 mm	Bygghöjd (tum)	3,346 inch
Bredd	10,3 mm	Byggbredd (tum)	0,406 inch
Nettovikt	1,94 g		

Säkringselement

Säkringslänksstandard	IEC 60269-6	Ström	20 A
Märkspänning DC	1 500 V		

Klassificeringar

ETIM 7.0	EC002704	ETIM 8.0	EC002704
ETIM 9.0	EC002704	ECLASS 11.0	27-14-20-02
ECLASS 12.0	27-14-20-02	ECLASS 13.0	27-14-20-02

Godkännanden

ROHS	Uppfyllelse
------	-------------

Nedladdningar

Teknikuppgifter Data	CAD data – Advanced Datasheet
Kataloger	Catalogues in PDF-format