

FUSE WSFL 10X85 25A 1K5V GPV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



gPV 10×85 cylindrical fuse cartridges are designed to provide compact, safe and economical protection of photovoltaic modules (field protection) with voltages up to 1,500 DC. They provide protection against both overload and short circuit (gPV class according to the requirements of IEC60269-6 and UL248-19 standards).

Allmänna beställningsdata

| | |
|-------------------|--|
| Artikelbeteckning | Fotovoltaik, Smältsäkringsinsats, 1500 V, 10x85, gPV, 25 A |
| Art.nr. | 4000002611 |
| Typ | FUSE WSFL 10X85 25A 1K5V GPV |
| GTIN (EAN) | 8430243419642 |
| Förp. | 50 Stück |

FUSE WSFL 10X85 25A 1K5V GPV

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Tekniska data

Mått och vikter

| | | | |
|-----------|---------|-----------------|------------|
| Höjd | 85 mm | Bygghöjd (tum) | 3,346 inch |
| Bredd | 10,3 mm | Byggbredd (tum) | 0,406 inch |
| Nettovikt | 1,96 g | | |

Säkringselement

| | | | |
|-----------------------|-------------|-------|------|
| Säkringslänksstandard | IEC 60269-6 | Ström | 25 A |
| Märkspänning DC | 1 500 V | | |

Klassificeringar

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 7.0 | EC002704 | ETIM 8.0 | EC002704 |
| ETIM 9.0 | EC002704 | ECLASS 11.0 | 27-14-20-02 |
| ECLASS 12.0 | 27-14-20-02 | ECLASS 13.0 | 27-14-20-02 |

Godkännanden

| | |
|------|-------------|
| ROHS | Uppfyllelse |
|------|-------------|

Nedladdningar

| | |
|----------------------|---|
| Teknikuppgifter Data | CAD data – Advanced Datasheet |
| Kataloger | Catalogues in PDF-format |