

FUSE WSFL 10X85 30A 1K5V GPV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

gPV 10×85 cylindrical fuse cartridges are designed to provide compact, safe and economical protection of photovoltaic modules (field protection) with voltages up to 1,500 DC. They provide protection against both overload and short circuit (gPV class according to the requirements of IEC60269-6 and UL248-19 standards).

Allgemeine Bestelldaten

Ausführung	Photovoltaik, Schmelzsicherungseinsatz, 1500 V, 10x85, gPV, 30 A
Best.-Nr.	4000005431
Typ	FUSE WSFL 10X85 30A 1K5V GPV
GTIN (EAN)	8430243440424
VPE	50 Stück

FUSE WSFL 10X85 30A 1K5V GPV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technische Daten****Abmessungen und Gewichte**

Höhe	85 mm	Höhe (inch)	3,346 inch
Breite	10,3 mm	Breite (inch)	0,406 inch
Nettogewicht	0,2 g		

Sicherungspatrone

Sicherungseinsatz Standard	IEC 60269-6, gPV (EN 60269-6)	Strom	30 A
Bemessungsspannung DC	1.500 V	Bemessungsausschaltvermögen	10 kA
Material Kontakte	versilbert	Max. Verlustleistung	5,5 W

Klassifikationen

ETIM 7.0	EC002704	ETIM 8.0	EC002704
ETIM 9.0	EC002704	ECLASS 11.0	27-14-20-02
ECLASS 12.0	27-14-20-02	ECLASS 13.0	27-14-20-02

Zulassungen

ROHS	Konform
------	---------

Downloads

Kataloge	Catalogues in PDF-format
----------	--