

**FUSE WSFL 10X85 30A 1K5V GPV****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

gPV 10×85 cylindrical fuse cartridges are designed to provide compact, safe and economical protection of photovoltaic modules (field protection) with voltages up to 1,500 DC. They provide protection against both overload and short circuit (gPV class according to the requirements of IEC60269-6 and UL248-19 standards).

**Allmänna beställningsdata**

Artikelbeteckning	Fotovoltaik, Smältsäkringsinsats, 1500 V, 10x85, gPV, 30 A
Art.nr.	<a href="#">4000005431</a>
Typ	FUSE WSFL 10X85 30A 1K5V GPV
GTIN (EAN)	8430243440424
Förp.	50 Stück

## FUSE WSFL 10X85 30A 1K5V GPV

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Tekniska data

## Mått och vikter

Höjd	85 mm	Bygghöjd (tum)	3,346 inch
Bredd	10,3 mm	Byggbredd (tum)	0,406 inch
Nettovikt	0,2 g		

## Säkringselement

Säkringslänksstandard	IEC 60269-6, gPV (EN 60269-6)	Ström	30 A
Märkspänning DC	1 500 V	Märkbrytförmåga	10 kA
Material kontakter	försilvråd	Effektförbrukning, max.	5,5 W

## Klassificeringar

ETIM 7.0	EC002704	ETIM 8.0	EC002704
ETIM 9.0	EC002704	ECLASS 11.0	27-14-20-02
ECLASS 12.0	27-14-20-02	ECLASS 13.0	27-14-20-02

## Godkännanden

ROHS	Uppfyllelse
------	-------------

## Nedladdningar

Kataloger	<a href="#">Catalogues in PDF-format</a>
-----------	------------------------------------------