

RKDG D15 PT6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Intelligent cabling solutions can save you valuable time and money.**

The FieldPower® modular system contains the right solution for every cabling task.

Foldable seals for the use of pre-assembled cables

Seals available with M16 and M20 connection thread
Integration of operating and signalling devices into the seal possible

General ordering data

| | |
|------------|--|
| Version | Field Power® sealing insert, Foldable seal, IP65 with corresponding housing, IP65, with corresponding enclosure, EPDM, 13 mm ² , 15 mm ² |
| Order No. | 4323220000 |
| Type | RKDG D15 PT6 |
| GTIN (EAN) | 4032248641222 |
| Qty. | 10 pc(s). |

RKDG D15 PT6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

| | | | |
|------------|---------|-----------------|------------|
| Depth | 18 mm | Depth (inches) | 0.709 inch |
| Height | 33.8 mm | Height (inches) | 1.331 inch |
| Width | 46.7 mm | Width (inches) | 1.839 inch |
| Net weight | 23 g | | |

Temperatures

| | | | |
|---------------------|----------------|-----------------------|----------------|
| Storage temperature | -40 °C...85 °C | Operating temperature | -40 °C...85 °C |
|---------------------|----------------|-----------------------|----------------|

General data

| | | | |
|--|---|---------------------------|--------------------|
| Material | EPDM | Silicone | No |
| Colour | black | Design | Foldable seal |
| Protection degree | IP65 with corresponding housing, IP65, with corresponding enclosure | UL 94 flammability rating | HB |
| Mounting position, installation notice | in FieldPower® sealing slot | Line type | round |
| Clamping range, min. | 13 mm ² | Clamping range, max. | 15 mm ² |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002624 | ETIM 7.0 | EC002624 |
| ETIM 8.0 | EC002624 | ETIM 9.0 | EC002624 |
| ECLASS 9.1 | 27-18-27-90 | ECLASS 10.0 | 27-18-28-15 |
| ECLASS 11.0 | 27-18-28-15 | ECLASS 12.0 | 27-18-28-15 |
| ECLASS 13.0 | 27-18-28-15 | | |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|---|--|
| Approval/Certificate/Document of Conformity | Manufacturer's Declaration FieldPower® Enclosure parts |
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |