

**FPL 4G1.5C4/Q8MW/2****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Take advantage of our pre-assembled FieldPower® connectors with HQ connectors acc. to IEC 23570 (DESINA) for connecting decentralised motor controller devices quickly and conveniently.

**General ordering data**

Version	FieldPower®, Cable, Metal housing, Number of wires: 4, Ölflex Servo 709 CY 4G1.5 + 2x(2x0.75), Cross-section: 1.5 mm <sup>2</sup> , 2 m
Order No.	<a href="#">8000005240</a>
Type	FPL 4G1.5C4/Q8MW/2
GTIN (EAN)	4032248997725
Qty.	1 pc(s).

**FPL 4G1.5C4/Q8MW/2****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Net weight 1 g

**Technical specifications for cable**

Bending radius, min., moving	222 mm	Bending radius, min., stationary	88,8 mm
Number of wires	4		

**General technical data**

Protection degree IP65

**Classifications**

ETIM 6.0	EC001578	ETIM 7.0	EC003250
ETIM 8.0	EC003250	ETIM 9.0	EC003250
ECLASS 9.0	27-06-20-11	ECLASS 9.1	27-06-90-90
ECLASS 10.0	27-06-01-06	ECLASS 11.0	27-06-01-06
ECLASS 12.0	27-06-01-06	ECLASS 13.0	27-06-01-06

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1
SCIP	edb4769d-47d5-4f66-921a-c1f4685d793c

**Approvals**

ROHS Conform

**Downloads**Catalogues [Catalogues in PDF-format](#)

## FPL 4G1.5C4/Q8MW/2

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

