

TS35X7.5 ST FPC 20 VER**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

Similar to illustration

Accessories

General ordering data

Version	Rail, TS 35, TS 35 x 7.5, Width: 165 mm, with slot, without slot, Steel, galvanized, chromium-plated
Order No.	8000037558
Type	TS35X7.5 ST FPC 20 VER
GTIN (EAN)	4050118653229
Qty.	20 pc(s).

Creation date April 28, 2024 11:10:35 PM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.

TS35X7.5 ST FPC 20 VER**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	7.5 mm	Depth (inches)	0.295 inch
Height	35 mm	Height (inches)	1.378 inch
Width	165 mm	Width (inches)	6.496 inch
Net weight	60 g		

General information

Installation advice	Direct mounting	Integral fixing	Screwed
Material	Steel	Material thickness	1 mm
Standards	DIN EN 60715	Surface finish	galvanized, chromium-plated

Classifications

ETIM 6.0	EC001285	ETIM 7.0	EC001285
ETIM 8.0	EC001285	ETIM 9.0	EC001285
ECLASS 9.0	27-40-06-02	ECLASS 9.1	27-40-06-02
ECLASS 10.0	27-40-06-02	ECLASS 11.0	27-40-06-02
ECLASS 12.0	27-40-06-02	ECLASS 13.0	27-40-06-02

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format