

**PV 40201S2V3C1A0ES****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Designed to work with different string inverters, Weidmüller has developed standard configurations of AC combiner boxes based upon recurring customer requirements. Depending on the version, the boxes can contain fuses and surge protection. These combiner boxes are specially designed for a measure string inverters manufacturers worldwide.

**Allmänna beställningsdata**

Art.nr.	<a href="#">8000069109</a>
Typ	PV 40201S2V3C1A0ES
GTIN (EAN)	4064675331315
Förp.	1 Stück

## PV 40201S2V3C1A0ES

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Tekniska data

## Mått och vikter

Djup	300 mm	Byggdjup (tum)	11,811 inch
Höjd	847 mm	Bygghöjd (tum)	33,346 inch
Bredd	636 mm	Byggbredd (tum)	25,039 inch
Nettovikt	20 295,234 g		

## Temperaturer

Omgivningstemperatur	-20 °C to +50 °C
----------------------	------------------

## Elektriska egenskaper AC

Jordning	TN-S, TN-C-S, TT & IT (EN 60364)	Märkspänning	690 V AC
Märkström	112,5 A		

## Ingångar AC

Antal ingångar AC	2
-------------------	---

## Normer och standarder

Normer	EN 61439-2:2011, IEC 61439-2 ed 3.0
--------	-------------------------------------

## Utgångar AC

Anslutningstyp AC-utgångsledning	M10, M12	Antal utgångar AC	1
----------------------------------	----------	-------------------	---

## GAK Kapsling

Monteringstyp	Montageplatta	Skyddsklass	IP65
---------------	---------------	-------------	------

## allmänna data

Normer	EN 61439-2:2011, IEC 61439-2 ed 3.0	Skyddsklass	IP65
--------	-------------------------------------	-------------	------

## ingångar

Mängd maximala effektpunkter	1 MPP	Säkringstyp	NH00
------------------------------	-------	-------------	------

## skyddskåpa

Isoleringsmaterial	Polyester glass-fibre reinforced, Polycarbonate	Monteringstyp	Montageplatta
--------------------	---	---------------	---------------

## Överspänningsskydd, DC-sida

Normer	EN 61439-2:2011, IEC 61439-2 ed 3.0
--------	-------------------------------------

## PV 40201S2V3C1A0ES

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Tekniska data

## Klassificeringar

ETIM 6.0	EC002928	ETIM 7.0	EC002928
ETIM 8.0	EC003857	ETIM 9.0	EC003857
ECLASS 9.0	22-57-92-03	ECLASS 9.1	22-57-02-90
ECLASS 10.0	22-57-02-90	ECLASS 11.0	22-57-02-92
ECLASS 12.0	22-57-02-92	ECLASS 13.0	22-57-02-92

## Miljööverensstämmelse för produkt

REACH SVHC Lead 7439-92-1

## Godkännanden

Godkännanden



## Nedladdningar

Användardokumentation	<a href="#">User Manual PV AC Combiner boxes</a> <a href="#">EU Declaration of Conformity</a>
Kataloger	<a href="#">Catalogues in PDF-format</a>

## PV 40201S2V3C1A0ES

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Ritningar

