

FBCON SS DP PCG TERM 24V**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

For Profibus DP and Modbus RS485, FBCon standard T-distributors and terminators connect individual field devices or remote I/O to the bus cable.

Their EMC cable glands, protection class IP66 and a wide operating temperature range safely protect your connections in harsh environments.

Functionality

- EMC cable glands for trunk and spurs
- M12 connector for spurs
- External earthing stud
- Pressure equalizing element
- Protection class IP66
- Aluminium and stainless-steel versions
- Profibus DP / Modbus RS485 compatible

Note: The use of FBCon products with aluminum enclosures and / or M12 connectors is not recommended in strongly saline environments.

General ordering data

Version	Standard distributor with bus termination (active), Terminator, IP66
Order No.	8714240000
Type	FBCON SS DP PCG TERM 24V
GTIN (EAN)	4032248404704
Qty.	1 pc(s).

FBCON SS DP PCG TERM 24V

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	36 mm	Height (inches)	1.417 inch
Width	58 mm	Width (inches)	2.283 inch
Length	64 mm	Length (inches)	2.52 inch
Net weight	404 g		

Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...75 °C
---------------------	----------------	-----------------------	----------------

Technical data

Bus system	Profibus-DP, Modbus RS485	Cable entry	plastic screwed cable gland
Connection type PE	Spur line with cable gland	Design of housing	With pressure compensation element
Housing main material	Stainless steel, rust-proof, Aluminum	Housing surface	polished
Operating voltage U_{max} , max.	32 V	Pollution severity	3
Protection degree	IP66	Type of distribution	Terminator
Type of mounting	surface-mounted		

Classifications

ETIM 6.0	EC001604	ETIM 7.0	EC001604
ETIM 8.0	EC001604	ETIM 9.0	EC001604
ECLASS 9.0	27-24-26-08	ECLASS 9.1	27-24-26-08
ECLASS 10.0	27-24-26-08	ECLASS 11.0	27-24-26-08
ECLASS 12.0	27-44-01-11	ECLASS 13.0	27-44-01-11

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	3a5f5913-76fc-4ff5-8563-4463f80bbe02

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E141197

Downloads

Approval/Certificate/Document of Conformity	Application notes – Certification UL Application notes – Declaration of Conformity
Product Change Notification	20220208 Technical change to FBCon field distributors (passive, with stainless steel housings)
User Documentation	Quick start guide – assembly instruction german / english Quick start guide – Application-Guide-Planning and installing Fieldbus networks-us-ing-FBCon_english_deutsch
Catalogues	Catalogues in PDF-format
Brochures	

Creation date April 29, 2024 3:32:27 AM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

