

IE-CT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The fully insulated plastic housings of our continuity testers are shockproof and unbreakable, making these instruments ideal for daily use, even in tough conditions. The integrated torch makes it easier to locate defective cables quickly and safely. The results of the continuity test can be conveyed visually and acoustically.

General ordering data

Version	Continuity tester for data cables
Order No.	8808420000
Type	IE-CT
GTIN (EAN)	4032248506002
Qty.	1 pc(s).

IE-CT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	36 mm	Height (inches)	1.417 inch
Width	70 mm	Width (inches)	2.756 inch
Length	140 mm	Length (inches)	5.512 inch
Net weight	396 g		

Measuring and testing devices

Display	digital	Supply	9V battery
---------	---------	--------	------------

Classifications

ETIM 6.0	EC002080	ETIM 7.0	EC002080
ETIM 8.0	EC002080	ETIM 9.0	EC002080
ECLASS 9.0	27-20-11-08	ECLASS 9.1	27-20-03-90
ECLASS 10.0	27-20-11-08	ECLASS 11.0	27-20-11-08
ECLASS 12.0	27-20-11-08	ECLASS 13.0	27-20-11-08

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	Manual MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN FL FIELDWIRING EN PI PROFINET CABLING EN