

IE-FM6Z2V00001MST0ST0X**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Assembled IE cables, FO patch cable, multimode, ST-ST,
orange, Core diameter 62.5 µm

General ordering data

Version	Patch cable, ST, ST IP 20, 62.5 µm, PVC, 1 m
Order No.	8813270000
Type	IE-FM6Z2V00001MST0ST0X
GTIN (EAN)	4032248513123
Qty.	1 pc(s).

IE-FM6Z2V00001MST0ST0X

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	1 m	Length (inches)	39.37 inch
Net weight	37 g		

Temperatures

Storage temperature	-25 °C...75 °C	Operating temperature	-5 °C...75
Installation temperature	-5 °C...50 °C		

General standards

Connector standard	IEC 61754-2
--------------------	-------------

Standards

Connector standard	IEC 61754-2
--------------------	-------------

Cable structure

Cable layout	ZIPCORD	Core diameter	62.5 µm
Material sheath	PVC	Primary coating	245 µm
Sheath diameter	3*6 mm	Sheathing colour	orange
Standard designations	I-V(ZN)Y		

Mechanical and material properties of cable

Min. bending radius, once only	30 mm	Min. bending radius, repetitive	60 mm
--------------------------------	-------	---------------------------------	-------

Plug

Plug left	ST, IP20, male contact, straight, plug, Plastic, unshielded	Plug right	ST, IP20, male contact, straight, plug, Plastic, unshielded
-----------	---	------------	---

Plug, left

Plug left	ST, IP20, male contact, straight, plug, Plastic, unshielded
-----------	---

Plug, right

Plug right	ST, IP20, male contact, straight, plug, Plastic, unshielded
------------	---

Classifications

ETIM 6.0	EC002607	ETIM 7.0	EC002607
ETIM 8.0	EC002607	ETIM 9.0	EC002607
ECLASS 9.0	27-06-10-03	ECLASS 9.1	27-06-10-03
ECLASS 10.0	27-06-10-03	ECLASS 11.0	27-06-10-03
ECLASS 12.0	27-06-10-03	ECLASS 13.0	27-06-10-03

IE-FM6Z2V00001MST0ST0X**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN

IE-FM6Z2V00001MST0ST0X

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Detailed drawing

