

IE-FM5D2UE0010MSD0SD0X**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Assembled IE cables, FO breakout cable, multimode, SC duplex - SC duplex, black, Core diameter 50 µm

General ordering data

Version	Dragline cable, SC duplex IP 20, SC duplex IP 20, 50 µm, PUR, 10 m
Order No.	8876430100
Type	IE-FM5D2UE0010MSD0SD0X
GTIN (EAN)	4032248609901
Qty.	1 pc(s).

IE-FM5D2UE0010MSD0SD0X

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	10 m	Length (inches)	393.701 inch
Net weight	309 g		

Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...80
Installation temperature	-20 °C...60 °C		

General standards

Connector standard	IEC 61754-4
--------------------	-------------

Standards

Connector standard	IEC 61754-4
--------------------	-------------

Cable structure

Cable layout	Break-out dragline	Core diameter	50 µm
Material sheath	PUR	Primary coating	245 µm
Sheath diameter	6 mm	Sheathing colour	black

Mechanical and material properties of cable

Bending cycles	100,000	Halogen	No
Min. bending radius, once only	25 mm	Min. bending radius, repetitive	77 mm

Plug

Plug left	SC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded	Plug right	SC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded
-----------	--	------------	--

Plug, left

Plug left	SC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded
-----------	--

Plug, right

Plug right	SC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded
------------	--

Classifications

ETIM 6.0	EC002607	ETIM 7.0	EC002607
ETIM 8.0	EC002607	ETIM 9.0	EC002607
ECLASS 9.0	27-06-10-03	ECLASS 9.1	27-06-10-03
ECLASS 10.0	27-06-10-03	ECLASS 11.0	27-06-10-03
ECLASS 12.0	27-06-10-03	ECLASS 13.0	27-06-10-03

IE-FM5D2UE0010MSD0SD0X**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN

IE-FM5D2UE0010MSD0SD0X

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Detailed drawing

