

**IE-FM6D2UE0001MSD0SD0X****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Assembled IE cables, FO breakout cable, multimode, SC duplex - SC duplex, black, Core diameter 62.5 µm

**General ordering data**

Version	Dragline cable, SC duplex IP 20, SC duplex IP 20, 62.5 µm, PUR, 1 m
Order No.	<a href="#">8876440010</a>
Type	IE-FM6D2UE0001MSD0SD0X
GTIN (EAN)	4032248609918
Qty.	1 pc(s).

## IE-FM6D2UE0001MSD0SD0X

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Length	1 m	Length (inches)	39.37 inch
Net weight	72 g		

## Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...80
Installation temperature	-20 °C...60 °C		

## General standards

Connector standard	IEC 61754-4
--------------------	-------------

## Standards

Connector standard	IEC 61754-4
--------------------	-------------

## Cable structure

Cable layout	Break-out dragline	Core diameter	62.5 µm
Material sheath	PUR	Primary coating	245 µm
Sheath diameter	6 mm	Sheathing colour	black

## Mechanical and material properties of cable

Bending cycles	100,000	Min. bending radius, once only	25 mm
Min. bending radius, repetitive	77 mm		

## Plug

Plug left	SC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded	Plug right	SC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded
-----------	--	------------	--

## Plug, left

Plug left	SC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded
-----------	--

## Plug, right

Plug right	SC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded
------------	--

## Classifications

ETIM 6.0	EC002607	ETIM 7.0	EC002607
ETIM 8.0	EC002607	ETIM 9.0	EC002607
ECLASS 9.0	27-06-10-03	ECLASS 9.1	27-06-10-03
ECLASS 10.0	27-06-10-03	ECLASS 11.0	27-06-10-03
ECLASS 12.0	27-06-10-03	ECLASS 13.0	27-06-10-03

**IE-FM6D2UE0001MSD0SD0X****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Environmental Product Compliance**

REACH SVHC

Lead 7439-92-1

**Approvals**

ROHS

Conform

**Downloads**

User Documentation

[MAN IE GUIDE DE](#)[MAN IE GUIDE EN](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

[FL FIELDWIRING EN](#)[PI PROFINET CABLING EN](#)[PI PROFINET CABLING EN](#)

**IE-FM6D2UE0001MSD0SD0X**

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Detailed drawing

