

**MEHA KP SW M-D-SPX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

- Flexible and solid wire with PVC, Teflon (PTFE) and silicone insulation
- No damage to the wire thanks to specially shaped blade
- No splicing of individual wires
- Blade inserts are easy to replace
- All inserts fit one housing
- Guide bars in the blade cassettes facilitate correct positioning of the wire in the tool

**General ordering data**

Version	Accessories, Set of cutters
Order No.	<a href="#">9003640000</a>
Type	MEHA KP SW M-D-SPX
GTIN (EAN)	4008190020507
Qty.	1 pc(s).

**MEHA KP SW M-D-SPX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	16 mm	Depth (inches)	0.63 inch
Height	11.5 mm	Height (inches)	0.453 inch
Width	26 mm	Width (inches)	1.024 inch
Net weight	3.68 g		

**Technical data**

Description of article	Set of blades for Mini-Duro-Stripax up to AWG 18 for PTFE
------------------------	---

**Stripping tools**

Cable type	Conductor with custom insulation	Colour	black
Max. conductor diameter	1.21 mm	Min. conductor diameter	1 mm
Stripping length, max.	7 mm	Stripping length, min.	3 mm

**Classifications**

ETIM 6.0	EC001509	ETIM 7.0	EC001509
ETIM 8.0	EC001509	ETIM 9.0	EC001509
ECLASS 9.0	21-04-92-37	ECLASS 9.1	21-04-48-90
ECLASS 10.0	21-04-92-37	ECLASS 11.0	21-04-48-91
ECLASS 12.0	21-04-48-91	ECLASS 13.0	21-04-48-91

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	