


H2,5/19D ZH BL SV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- in multi-pack bag (5 x 100 pcs.)
- DIN colour code
- other colour code

General ordering data

Version	Wire-end ferrule, Twin wire-end ferrule, 13 mm, 10 mm, blue
Order No.	9004430000
Type	H2,5/19D ZH BL SV
GTIN (EAN)	4008190099367
Qty.	250 pc(s).
Packaging	Multipack bag

H2,5/19D ZH BL SV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	0.328 g
------------	---------

Technical data

Description of article	Twin wire end ferrule, blue	Version	Twin wire-end ferrule
------------------------	-----------------------------	---------	-----------------------

Wire-end ferrules

Collar height (A)	8 mm	Collar width (B)	4.5 mm
Colour code	DIN	Conductor cross-section	2.5 mm ²
Contact surface diameter (D1)	2.8 mm	Contact surface length (L2)	10 mm
L1 in mm	19 mm	Metal sleeve thickness (S1)	0.15 mm
Plastic collar thickness (S2)	0.4 mm	Stripping length	13 mm
Wire connection cross section AWG, max.	AWG 14		

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ETIM 9.0	EC000005
ECLASS 9.0	27-40-02-01	ECLASS 9.1	27-40-02-01
ECLASS 10.0	27-40-02-01	ECLASS 11.0	27-40-02-01
ECLASS 12.0	27-40-02-01	ECLASS 13.0	27-40-02-01

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

Downloads

Engineering Data	CAD data – STEP
Engineering Data	Zuken E3.S
User Documentation	Technical information - EN Technical information - DE
Catalogues	Catalogues in PDF-format
Brochures	

H2,5/19D ZH BL SV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Drawings****Drawing**