

SDIS 0.6X3.5X100**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1.
SoftFinish grip

General ordering data

Version	Screwdriver, Screwdriver
Order No.	9008390000
Type	SDIS 0.6X3.5X100
GTIN (EAN)	4032248056354
Qty.	1 pc(s).
Delivery status	Discontinued
Available until	2021-04-30
Alternative product	2749810000

SDIS 0.6X3.5X100**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Width	205 mm	Width (inches)	8.071 inch
Diameter	23 mm	Net weight	34 g

Technical data

Description of article	VDE-insulated screw-driver with slotted blade 0.6x3.5x100
------------------------	--

Screwing tools

Blade length	100 mm	Blade thickness (A)	0.6 mm
Blade type	B	Blade width (B)	3.5 mm
Form	Slotted		

Classifications

ETIM 6.0	EC000158	ETIM 7.0	EC000158
ETIM 8.0	EC000158	ETIM 9.0	EC000158
ECLASS 9.0	21-04-04-07	ECLASS 9.1	21-04-04-07
ECLASS 10.0	21-04-04-07	ECLASS 11.0	21-04-04-07
ECLASS 12.0	21-04-04-07	ECLASS 13.0	21-04-04-07

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Downloads

Approval/Certificate/Document of Conformity	Manufacturer's Declaration - Screwdrivers Declaration of the Manufacturer
Catalogues	Catalogues in PDF-format
Brochures	