

SDS 0.4X2.5X75**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Slotted screwdriver with rounded blade SD DIN 5265,
ISO 2380/2, output to DIN 5264, ISO 2380/1. Chrom-
Top tip, SoftFinish grip

General ordering data

Version	Screwdriver, Screwdriver
Order No.	9009030000
Type	SDS 0.4X2.5X75
GTIN (EAN)	4032248266944
Qty.	1 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2021-03-31
Alternative product	2749320000

SDS 0.4X2.5X75**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Width	180 mm	Width (inches)	7.087 inch
Diameter	23 mm	Net weight	28 g

Technical data

Description of article	Screwdriver with slotted bit, 0.4 x 2.5
------------------------	---

Screwing tools

Blade length	75 mm	Blade thickness (A)	0.4 mm
Blade type	A	Blade width (B)	2.5 mm
Form	Slotted		

Classifications

ETIM 6.0	EC000158	ETIM 7.0	EC000158
ETIM 8.0	EC000158	ETIM 9.0	EC000158
ECLASS 9.0	21-04-04-07	ECLASS 9.1	21-04-04-07
ECLASS 10.0	21-04-04-07	ECLASS 11.0	21-04-04-07
ECLASS 12.0	21-04-04-07	ECLASS 13.0	21-04-04-07

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	b28ab223-64ec-44cf-adb0-4dd6ebcae141

Downloads

Approval/Certificate/Document of Conformity	Declaration of the Manufacturer
Catalogues	Catalogues in PDF-format
Brochures	